

# XLERATOR® HAND DRYER

## DEMO UNIT



**XL-BW**

White Thermoset Resin (BMC)

Excel Dryer has developed a demonstration model of our XLERATOR® Hand Dryer. This is a very effective and dynamic sales tool to utilize in the field or display in your showroom.

### INCLUDES

- ✓ Electrical Cord
- ✓ Plug
- ✓ Tripod Stand
- ✓ Custom Carton/Carrying Case
- ✓ Small Spray Bottle
- ✓ All cover options available

### INSTRUCTIONS

Your demo is shipped in a carton which will also serve as your carrying case (as shown here).

1. Press down on center section to unfasten flaps from each side.
2. Remove tripod stand from storage insert on top of box. Unlock and extend legs fully. Don't forget to re-lock legs.
3. Slide down and lock center brace by turning knob.
4. Turn black collar on tripod to unlock height adjustment crank handle. Raise center shaft all the way to top with crank. Be sure to re-lock the black collar.
5. Use finger holes on each end to lift tripod storage insert from box.
6. Remove dryer from box — carefully lift out and remove plastic bag. Save all packaging material (including plastic bag and tamper-proof wrench).
7. Install dryer on tripod as illustrated below, making sure to position the front of the dryer centered over "bubble leveler." Plug into standard electrical outlet.



1



2



3



7



# TIME TO THROW IN THE TOWEL®

EXCEL DRYER INC • 1.800.255.9235 • EXCELDRYER.COM